

HSM-4 Mini Heat Sealer

The satisfactory development, manufacture, conversion and application of flexible packaging films necessitates the implementation of precise methods of quality control systems. The HSM-4 was developed to precisely control the parameters essential in determining the heat seal threshold. Especially suited for flexible packaging materials, laminates, foils and paper, the HSM-4 features accurate control of temperature, pressure and dwell time of a standard surface area sealing jaw. With the introduction of a standard test method ASTM F2029 and our heat sealer HSM-4, you can be confident that your heat seal

threshold measurement is common to all producers, converters and end users of flexible packaging materials and their eventual applications.

The HSM-4 also features a unique method of quick change over jaws, the machine employs a slide-on jaw arrangement. The machines comes with dovetailed blank heater blocks, in single or dual option, where standard flat ground surface slide-on jaw is supplied. When profiled crimp sealing surface is needed, mating dovetailed slide-on jaw are replaced very easily.



UK & INTERNATIONAL RDM Test Equipment Ltd. 39 Gold Nursenies Business Park Jenkins Drive 39 Gold Nurseri Jenkins Drive Elsenham Hertfordshire CM22 6JX

AMERICAS RDM Test Equipment LLC. 441 Old Hwy 8 NW Suite 203 New Brighton Minneapol MN55112

Email: sales@rdmtest.com

Tel: +1 651 766 2565 Mobile:+1 651 485 2372 Email: sales@rdmtest.com

Specifications Temperature Control

0 - 300°C (0 - 572°F) 0.1°C resolution +/- 0.5% +/- 1 digit accuracy. Operating temperature accuracy +/- 2ºC. Resistance Type 'J' thermocouple sensing. Single independent or dual independent control

Pressure

0 – 100psi (0 – 6.8 bar, 0 – 689 Kpa) via dial pressure gauge. Pressure control through precision regulator. Repeatability +/-5.0 PSI Operation accuracy +/-10% Supply via factory compressed air line or nitrogen or compressed air bottles min 6 bar (90 psi) max. 7 bar(100 psi). Pressure medium must be clean and dry.

Dwell Time

0.1 - 99.9 sec. 0.1 sec resolution real time base via quartz crystal +/- 0.5% of range. Operating accuracy +/- 10% (taking into account friction in piston movement).

Footswitch

Connection port for footswitch operation. Optional footswitch.

Sealing Jaw Std

Single jaw option: Top heated with silicone rubber (60 shore hardness) 5mm – 25mm wide x 50mm long. Jaws made from aluminium with machine ground flat face.

Dual jaw option: Top and Lower heated 5mm - 25mm wide x 50mm long. Jaws made from aluminium with machine ground flat face.

Environment

5-50C ambient operating temperature, RH 75% max (non-con densing)

Power

240V AC 50/60 Hz (110V AC voltage available on request)

Options

Footswitch.

PVC Dust cover.

Up-grade to digital dwell timer. Crimp profiled slide-on jaws 120 deg x 1.8 mm pitch.

Cold Seal Option (temperature circuit re-moved) supplied with flat or crimp profiled jaws.

Teflon coated tape or permanent Teflon coating Digital thermometer and s/s band probe to check the actual temperatures of sealing Jaw.



AMERICAS RDM Test Equipment LLC. 441 Old Hwy 8 NW Suite 203

RDM Test Equipment Ltd. 39 Gold Nurseries Business Park Jenkins Drive Elsenham Hertfordshine CM22 6JX

Minneapol MN55112 Tel: +1 651 766 2565 Mobile:+1 651 485 2372 Email: sales@rdmtest.com

Email: sales@rdmtest.com